

The manual provided is designed to cover the standard configurations for the chamber you ordered. Any special features or optional items ordered are presented below.

Your chamber is equipped with the following:

- Temperature ranges of 2°C to 44°C ± 0.5°C (lights off) and 7°C to 44°C ± 0.5°C (lights on).
- Humidity range 50 to 85% ± 10% over 15°C to 30°C (lights off).
- Light intensity of 125 $\mu\text{moles} / \text{m}^2 / \text{sec}$ as measured 6" from the light fixtures at a temperature of 24°C and a light lifetime of 100 hours.
- IncuWhite™ linear LEDs
- Open loop dimmable lighting *
- Pan type humidifier and dehumidifier with Vaisala HMP60 relative humidity sensor.
- Condensate drain line routed out rear wall of chamber *
- Air-cooled condensing unit

* - Please refer to the section titled Associated Diagrams, Schematics and Miscellaneous Information for special installation and/or operation instructions.

Your chamber does not include the following options as described in the manual:

- No remote alarm contacts are provided.
- No air blocks are provided.

Note: All supplemental information supersedes any similar information provided in the standard manual.